



CK22M

Fast response contact surface probe, 45 degree angle swivel head sensor



Copyright © 2007 Test Products International, Inc.

Application

Contact temperatures on flat and uneven surfaces

Range°F°C

-58° to 932°F
-50° to 500°C

Probe tip

32

Dimensions

Stem Length: 4.5" (114mm)
w/45° bend
Diameter: 0.6" (15mm)
Lead Length: 39.4" (1M)

Insulation Material

Polyurethane