



Generic photo of the product

Main technical characteristics of this part number

Family	XCMD cable
Type of head	Metal plunger
Special features of the head	-
Operator head	Plunger
Operating head	With metal plunger
Action of angular movement	-
Operator	On end
Speed of attack max	0.5m/s
Min torque	8,5 N
Connection	Removable PvR cable 2m
Material - case	Metal
Dimensions of body (mm)	30 x 50 x 16
Mounting method	Body
Contact unit	N/O+N/C
Contact to operate	Snap action
Positive complete product	Yes
Form of contact	Zb
No. of steps	1
Degree of protection	IP67
Temperature of operation	-25...+70°C

Generic description of the product

Osiswitch XCMD modular limit switch with 2m cable
Miniature metallic position switches, connection by 2 m long cable fastening by the body or by the head on some models.