



Masking Film

7300 Series

Technical Data

October, 2011

Product Description

3M™ 7300 Series Masking Film is a high performance, high temperature wide area masking film that is soft flexing for good drape and conformability.

Product Construction

Backing	Adhesive	Color	Standard Roll Length
Polypropylene Film	None	Translucent	1500 ft. (457 m)

Typical Physical Properties

Note: The following technical information and data should be considered representative or typical only, and should not be used for specification purposes.

		ASTM Test Method
Tensile Strength (MD):	7.4 lbs./in. width (130 N/100 mm)	D-3759
Elongation at Break:	680%	D-3759
Thickness (Embossed):	3.4 mils (86 micrometers)	D-3652
Temperature Use Range:	Up to 310°F (155°C) for 60 minutes	

Features

- 3M™ 7300 Series Masking Film is ideal for protecting against bleed-through of solvents and paints.
- Conformable film with good drape properties.
- Eliminates flying fiber contamination normally associated with fibrous paper wide area masking products.
- Treated backing for good paint adhesion.
- Many 3M masking tapes have excellent adhesion to 3M™ 7300 Series Masking Film.
- Masking tape and film can be dispensed together using existing 3M apron tapers.
- Textured surface unwinds smoothly from roll.
- Soft film resists scratching of clear coat protective layer.
- Excellent paint flaking resistance.

Application Ideas

- Tutone paint masking for automobiles, trucks, buses and boats.
- Repair painting of automobiles and trucks.
- Automotive fascia piece part paint masking.

3M™ Masking Film

7300 Series

Storage	Store under normal conditions of 70°F (21°C) and 50% R.H. in the original carton.
----------------	---

Shelf Life	To obtain best performance, use this product within 12 months from date of manufacture.
-------------------	---

Technical Information	The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.
------------------------------	--

Product Use	Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.
--------------------	--

Warranty, Limited Remedy, and Disclaimer	Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.
---	---

Limitation of Liability	Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.
--------------------------------	--

ISO 9001:2008

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2008 standards.



Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (Fax)
www.3M.com/industrial



*Recycled Paper
40% pre-consumer
10% post-consumer*

3M is a trademark of 3M Company.
Printed in U.S.A.
©3M 2011 70070944981 (10/11)