


OBSOLETE- USE MSR320R**Specificatio**

Sound level Category	Medium Sound Level
Mode of Operation	Continuous
Mounting	Printed Circuit Board (see note B)
Voltage Rating	3 to 20 Vdc
Frequency	3400 Hz \pm 400 Hz
Loudness (Min. Voltage)	62 dB(A) min. @ 2 FT and 3 Vdc
Loudness (Max Voltage)	80 dB(A) min. @ 2FT and 20 Vdc
Current Draw	3 mA Max @ 3 Vdc
Current Draw	16 mA Max @ 20 Vdc
Storage Temperature	-30°C to +80°C
Operating Temperature	-20°C to +65°C
Weight (Typical)	3.5 grams
Housing	Valox (UL94V-0), Color Blue
Options	For other options contact factory

Dimensions: Inches (mm)

NOTE A:
TERMINALS - .031" DIA. NICKEL/TIN COATED BRASS.

NOTE B:
MOUNTING- INSERT INTO PRINTED CIRCUIT BOARD AND HAND OR MACHINE SOLDER.
UNITS DO NOT HAVE A WASH LABEL AND ARE NOT SUITED FOR AQUEOUS WASH. SEE
P/N MSR320S IF WASH LABEL IS NEEDED. RECOMMENDED MAXIMUM TEMPERATURE AND
TIME DURATION IS +270°C AND 3 SECONDS RESPECTIVELY.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[MSR320](#)