




RE321-LF

- Epoxy fibre-glass FR4 1.50 mm
- Double-sided 35 µm Cu
- Plated through holes (PTH)
- Hot air leveling (HAL-leadfree)
- Hole spacing 2.54 x 2.54 mm
- 36 x 55 soldering pads 2.00 x 2.200 mm
- Hole diameter 1.00 mm
- Connector 32/64/96-channel DIN 41612 grid 2.54 mm type C
- Size 100 x 160 mm

ver.20141024