

Material	High Conductivity Seamless Copper Tube
Plating	Electro-Tin
Wire Size	400 kcmil
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric
Wire Strip Length	1-9/16 in.
Stud Size	3/8 in.
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.
UL Temperature Rating	90° C
C.S.A Certified Wire Connector	Yes
Panduit Color Code on Barrel	BLUE
Panduit Die Index No. on Barrel	P76
Alternate Industry Die Index No. () on Barrel	(19)

						 PANDUIT CORP. TINLEY PARK, ILLINOIS	
						LCAN400-38-6 Copper Lug - One-Hole, Narrow Tongue, Standard Barrel	
01	1/11	JHNU	JHNU	REVISED OVERALL LENGTH: WAS 3.22 REVISED TONGUE THICKNESS: WAS .18			
REV	DATE	BY	CHK	DESCRIPTION		ECN	SCALE N/A DRAWING NO / CAD FILE LCAN400-38-CUST