


CS-Lxx-Dx-xx

NYLON CLEARANCE SPACERS



PRODUCT INFORMATION

- **Material:** Nylon 6
- **Operating Temperature:** -30°C to +80°C
- **Minimum Order:** 300 Pieces
- **Free samples available on request**

- **Listed below are our standard lengths. However, please enquire about any non standard requirements you may have**

PRODUCT TABLE

SAMPLE CODE: CS-L15-D8-43

CS = Clearance Spacer **L** = Length **D8** = 8.0 O/D **43** = 4.3 I/D

OTHER SIZES AVAILABLE ON REQUEST

Clearance	Product Code	Body Length (L) (Replace ** in code with required body length)
M3	CS-L**-D6-32	2, 3, 4, 5, 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24, 25, 26, 27, 28, 29, 30
M4	CS-L**-D8-43	2, 3, 4, 5, 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24, 25, 26, 27, 28, 29, 30
M5	CS-L**-D10-52	2, 3, 4, 5, 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24, 25, 26, 27, 28, 29, 30

the **vital**
component