




SVS ECO LED VALVE PLUG FORM A 18MM LED VDR 24V

2+PE field-wireable M16x1.5

Form A (18 mm)
24 V AC/DC with LED and VDR
metric

[Link to Product](#)**Illustration**

stay connected

Height: 31 mm

Product may differ from Image

Approvals



Form

29005

Technical Data

Operating voltage	24 V AC/DC $\pm 10\%$
Operating current per contact	max. 1.5 A
Connection cross section	0.5...1.5 mm ²
Sealing range (cable diameter)	6...8 mm
Locking of ports	M3 (recommended torque 0.4 Nm)
Compression gland	M16 $\times$ 1.5 mm
Contact figure	Cable outlet can be turned in 90° steps
Protection	IP65 inserted and tightened

General data

Temperature range	-40...+60 °C
-------------------	--------------

Commercial data

country of origin	HU
customs tariff number	85369010
minimum order quantity	1