

Fuses & Switches - Nylon and Phenolic



Fuse Block Strap Screw



Fuse Block Strap Clamp



Fuse Block Tubular Screw

Type of Block	Fuse Block Strap Screw	Part Number	Fuse Block Strap Clamp	Part Number	Fuse Block Tubular Screw	Part Number
0300 Series - Nylon						
Channel Mount (Dovetail Base) Nylon	0311	CPGI-BUCH-1437397-1	0318	CPGI-BUCH-1437397-3	0312	CPGI-BUCH-1437397-2
Contact Type						
Specifications						
Wire Range (AWG) Solid & Stranded	22-8		18-8		18-8	
Wire Strip Length (in.)	—		1/2		1/2	
Screw Type	10-32 binding head		8-32 pan head w/clamp		1/4"-28 set screw	
Ampacity						
	25 A		25 A		25 A	
End Sections						
Channel Mount, Nylon	CPGI-BUCH-2-1437397-0		CPGI-BUCH-2-1437397-0		CPGI-BUCH-2-1437397-0	



Strap Screw



Strap Clamp



Tubular Screw

Type of Block	Strap Screw	Part Number	Strap Clamp	Part Number	Tubular Screw	Part Number
0300 Series - Phenolic						
Direct Mount (Flat Base) Fuse Block with Puller	351	CPGI-BUCH-2-1437397-8	358	CPGI-BUCH-3-1437397-1	352	CPGI-BUCH-3-1437397-0
Channel Mount (Dovetail Base) Fuse Block with Puller	0351	CPGI-BUCH-1437397-9	0358	CPGI-BUCH-1-1437397-2	0352	CPGI-BUCH-1-1437397-0
Contact Type						
Specifications						
Wire Range (AWG)	22-8		18-8		18-8	
Solid & Stranded	—		1/2		1/2	
Wire Strip Length (in.)	8-32		8-32		1/4"-28	
Screw Type	binding head		pan head w/clamp		set screw	
Ampacity						
Fuse Blocks	25A		25A		25A	
Switch Blocks	15A		15A		15A	
End Sections						
No Contact, Flat Base	CPGI-BUCH-2-14376397-4		CPGI-BUCH-2-14376397-4		CPGI-BUCH-2-14376397-4	
No Contact, Dovetail Base	CPGI-BUCH-14376397-5		CPGI-BUCH-14376397-5		CPGI-BUCH-14376397-5	