


HBLFRSBK-- Single Pole Devices



Male Receptacle, Threaded

400 Amp Stud Type Panel Mount Female Receptacle, Black

Product Specifications	
Product Version	section/images/receptacles.jsp
Receptacle Type	Panel Mount Female Receptacle
Type	For Through Mounting Holes
Amperage	400 A
Connection Method	Stud Type
Color	Black



Panel Mount Receptacle; 1/2"-13 UNC Thread Stud

A	B	C	D	E
2.20" (55.9)	2.20" (55.9)	1.50" (38.1)	4.10" (104.3)	1.48" (37.6)

Dimensional Diagram

Ampacity Chart (Type SC/PPC Wire)

Cable Size	Ampacity*
#4	140
#2	190
2/0	300
4/0	405

* 90 Deg. C column NEC Table 400.5(B).

Ampacity Table