





ISS	ZONE	REVISIONS	DESCRIPTION\PER REQUEST\DATE



RECOMMENDED
CABLE STRIPPING DIM'S



1. CRIMPED CONTACT PIN
HEX CRIMP SIZE .100"



NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)

1. BRASS PER QQ-B-626
2. BRASS PER QQ-B-613
3. NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
4. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
5. PTFE MIL-P-19468

11	CONTACT PIN	NOTE 1	NOTE 4	1	MS000-8-3/14-C
10	HEX NUT	NOTE 1	NOTE 3	1	BS200-14-11/54
9	WASHER	NOTE 2	NOTE 3	1	WS-10/8X05
8	GASKET	SILICONE	RED	1	BS200-12
7	BRAID CLAMP	NOTE 1	NOTE 3	1	BS200-11-54/45-B
6	RETAINER RING	SUS 304	NATURAL	1	MS000-7-C
5	GASKET	SILICONE	RED	1	GS-156/8X15
4	CONTACT BODY	NOTE 1	NOTE 3	1	MS000-5
3	INSULATOR	NOTE 5	NATURAL	1	MS000-4T-50-A
2	BODY	NOTE 1	NOTE 3	1	MS200-2
1	SHELL	NOTE 1	NOTE 3	1	MS000-1-B
NO.	DESCRIPTION	MATERIAL	FINISH	QTY	DRAWING NO.

DIMENSIONS ARE IN MILLIMETERS
UNLESS OTHERWISE SPECIFIED
TOLERANCES

- 0.5-6 ±0.2
- 6-30 ±0.4
- 30-120 ±0.6
- 120-315 ±1
- 315-1000 ±1.6
- 1000-2000 ±2.4

PART NO. N1141A1-NT3G-1-50

APPROVED

DATE

CHECKED

DATE

DRAWN

DATE

Amphenol

N CLAMP PLUG
(FOR RG-58C/U,58/U,142A/U,223/U)

DRAWING NO. KJ-N1141A1-NT3G-58U-50

ITEM NO.