


LEDs & INDICATORS

515 MPA Series

- Threaded body for panel thicknesses 0.5-3.5mm, panel cut-out 6.4mm diameter
- Stripped wire termination 164mm long, PVC
- LED, Filament 6-28V 30-40mA and Neons 125-240V 0.8-1mA, as standard
- Neon-replacement LED version is fitted with a resistor and operates at 240V AC. Operating life 50,000 hours
- Polycarbonate lens/body, chrome bezel, supplied with nut and shakeproof washer
- Red, green, amber, clear, blue and opal lens colour options as standard
- Maximum working temperature 105°C
- Custom wire lengths and specification to order



TYPE NO.		515	1	05 - XXXX	- T /	XXX
515 Series Indicator		515				
Lens Type	Trapezoid	1				
	Top Hat	2				
Stripped wire 164mm long		05				
LED pins		13				
LED, black cathode & white anode wires		LED				
LED, neon-replacement 240V 1mA		LED2				
Filament 6V 40mA, white wire		640				
Filament 12V 35mA, yellow wire		1235				
Filament 14V 40mA, yellow wire		1440				
Filament 24V 35mA, green wire		24				
Filament 28V 30mA, green wire		28				
Neon 125V 1mA, blue wire		125				
Neon 240V 0.8mA, red wire		240				
Transparent lens		T				
Lens colour Red		RED				
Lens colour Green		GRN				
Lens colour Amber		AMB				
Lens colour Clear		CLR				
Lens colour Blue		BLU				
Lens colour Opal		OPL				

Body Dimensions

