



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



-ADHESIVE BACK PRESSURE
SENSITIVE FOAM TAPE
.040(1.0) THICK WITH
PROTECTIVE LINER.

NOTES: SEE

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLORS AND OR PACKAGE QUANTITY.
2. PART IS DESIGNED TO SUPPORT MAXIMUM WEIGHT ON A CLEAN, DRY, SMOOTH SURFACE.
3. TO APPLY PART:
 - a. REMOVE PROTECTIVE LINER.
 - b. PLACE PART IN DESIRED LOCATION.
 - c. APPLY PRESSURE TO FLAT SURFACE OF PART.
4. DIMENSIONS IN PARENTHESES ARE IN METRIC.
5. NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. THE CONDITIONS UNDER WHICH THESE RACEWAYS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.

PART NAME	PANDUIT PART NO. (** SEE NOTE 1)	LENGTH IN. (MM)	STATIC LOAD (SEE NOTE 2)	APPROXIMATE WEIGHT
SOLID WALL DUCT	LDS3**10-A	120.0 ±.12 (3048.0 ±3.0)	.29 LB/IN (5.2 g/mm)	.050 LB/FT (.074 g/mm)

	CAD FILENAME/LAYERS	D35541CO_SOLID_LDS3_02.RT
	PANDUIT CORP. TINLEY PARK, ILLINOIS	SOLID WALL DUCT (LDS3) CUSTOMER DRAWING
	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ±.010 (.4) (.XX) ±.03 (.8) ANGLES ±	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.
2	03-08-04 JHEP RGRD C. REMOVED PART NUMBER LDS3**2-A	RGRD RGRD
I	09-17-98 PM B. REVISE NOTES A. REVISE CHART; ADD 2M LENGTH	H1W H1W
R	09-24-96 JBA CEF RELEASED TO PRODUCTION	CEF CEF
REV	DATE BY CHK DESCRIPTION ECN CHK CUST SUP	CHECKED BY CEF
		DWG NO. DRAWING NO. SCALE NONE
		A SIZE