


Dimensions: mm (In.)

**Electrical Specifications:**

- Rating: .5A/125VAC/12VDC
- Insulation Resistance: 100M Ω min. @ 500VDC
- Dielectric Strength: 250VAC for 1 minute
- Contact Resistance: 20m Ω max.

Mechanical Specifications:

- Mechanical Life: 5000 min.
- Operating Temperature: -10°C to +60°C
- Circuit: 2P SPST Off-(On)

Materials:

- Nut: Nickel plated steel
- Washer: Uni-chromium plated steel
- Terminals: Silver plated brass
- Spring: Piano wire
- Stopper, knob: ABS
- Contacts: Tin plated brass
- Body: Plastic
- Bushing: Nickel plated brass

Note:

- RoHS Compliant

Mouser Stock No.	Button Color
104-0010	White
104-0012	Red
104-0013	Black
104-0011	Green

Pushbutton Switches

104-0010, 104-0011, 104-0012, 104-0013

Mountain Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[104-0012](#)

Other:

[104-0013](#) [104-0011](#) [104-0010](#)