



FEATURES:

- Provides a simple means of connection between equipment with both SMA and Type N jacks.
- SMA and N connectors feature PTFE dielectric and tarnish resistant shells for superb electrical performance.
- Gold center contacts assure noise free connections.

MATERIALS:

Type N Male: Body and Fittings – Brass, Tarnish Resistant

Center Contact – Brass, Gold Plated

Dielectric - PTFE

Coaxial Cable: RG142B/U, Double Shielded, O.D. .195" (4.95mm)

SMA Male: Body and Fitting – Steel, Finish – Passivated Steel

Center Contact – Brass, Gold Plated

Dielectric – PTFE

RATINGS:

Operating Temperature: +200°C (+329°F) Max.

Operating Voltage: 335 VRMS Max.

Connector/Cable Impedance: 50 Ohms

ORDERING INFORMATION: Model 5058-X-xx

xx = Cable Length in Inches, Standard Lengths: 12" (30.48cm), 24" (61cm), 36" (91.44cm), 48" (122cm), 60" (152.4cm)

Additional lengths can be quoted upon request.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[5058-X-48](#) [5058-X-36](#) [5058-X-12](#) [5058-X-60](#)