

OBSOLETE- USE PB-1220PQ

Specifications

Oscillation Frequency (Hz)	2048
Operating Voltage (Vp-p)	1.25 ~ 2.5
Rated Voltage (Vp-p)	1.5
Current Consumption Max. (mA)	40 at Rated Voltage
Sound Pressure Level Min. (dB)	85 at 10cm at Rated Voltage
Coil Resistance (Ω)	16 ± 2
Operating Temperature ($^{\circ}\text{C}$)	$-20 \sim +70$
Storage Temperature ($^{\circ}\text{C}$)	$-30 \sim +80$
Housing	ABS 707 UL94HB plastic resin (Color: Black)
Leading Pin	Tin Plated Brass
Weight (Grams)	1.4
Options	For other options contact factory

PS: Vp-p = 1/2duty, square wave

Dimensions: (units: mm)

