

Item # 10069, Hour Meters (ETIs)

Hour Meters (ETIs)



Model 635G Non-Resettable Round
Round Style "G" measures ø2.687"

Time registration includes tenths increments i.e.: Hours/Tenths, Minutes/Tenths and Seconds/Tenths.
Image shown in HOURS.
Product shows MINUTES increments.

[SPECIFICATIONS](#) · [ELECTRICAL RATINGS AVAILABLE](#)

SPECIFICATIONS

Model	635 G
Time Increments	MIN
Resettable	-
Non-Resettable	Y
Reset Type	-
Bezel Shape	Round Style G
Bezel Size	ø2.687"
Body Depth	2.5"
Body Diameter	ø2.20"
Mounting Style	3 Screw Panel
Operating Temperature Low	-4 °F
Operating Temperature High	131 °F
Approvals	UL/cUL

ELECTRICAL RATINGS AVAILABLE

Voltage	115 V
Frequency	60 Hz
Current Type	AC
Power	2.7 Watts
