



(5.08 mm) .200"

PSS-13-01-T-S

PSS-08-01-T-S

PSS SERIES

POWER SOCKET STRIP

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?PSS

Insulator Material:

Black LCP

Contact Material:

BeCu

Plating:

Sn over 50 μ " (1.27 μ m) Ni

Current Rating (PSS/FWS):

11.4 A per pin

(1 pin powered)

Current Rating (PSS/HPM):

11.0 A per pin

(1 pin powered)

Voltage Rating:

625 VAC/884 VDC

Insertion Depth:

(2.62 mm) .103" to

(5.03 mm) .198"

RoHS Compliant:

Yes

Mates with:

FWS, HFWS,
SW, HPM, HPW

PROCESSING

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0.15 mm) .006" max (02-14)*

(0.20 mm) .008" max (15-20)*

*(.004" stencil solution

may be available; contact



ipg@samtec.com)

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



FILE NO. E111594



Note:

Some lengths, styles and options are non-standard, non-returnable.

WWW.SAMTEC.COM

Unless otherwise approved in writing by Samtec, all parts and components are designed and built according to Samtec's specifications which are subject to change without notice.