

main menu



home

test & measurement

products

skills

download

online catalogue T&M

clamp-type test probes

crocodile clips

test probes

oscilloscope test probes

measuring leads

plugs

sockets

- ▶ 2 mm system
- ▶ 2 mm safety system
- ▶ 4 mm system
- ▶ 4 mm safety system

sets

miscellaneous

company

portrait

corporate association

location maps

fairs and exhibitions

jobs

imprint

terms and conditions

Home ▶ sockets ▶ sockets ▶ KUN S

KUN S

 datasheet for KUN S
 article number: 934096104


View Full-Size Image



search online catalogue

Search

Search

Messetermine

No events

QR-Code



product description:	order number: 934 096-104
description:	Safety coupling with screw connection for leads from 0.5mm ² to 1.5mm ² , outer diameter of lead max. 4,2mm Connectable with plugs 4mm and safety plugs 4mm 1000V-system, IEC 61010. Simple assembly by "Click-System".
typ:	KUN S gruen/green
system:	4 mm safety system
order number:	934 096-104
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT III
type of contact:	unsprung socket Ø 4 mm
type of termination:	screw
rated voltage:	AC/DC 1000 V
rated current:	24 A
Please consider derating curve!	
material	
contact material:	brass
contact surface material:	nickel
housing material:	PA
environmental conditions:	
temperature range:	-15 °C to +70 °C
flammable class:	
housing (basic material):	UL 94 V - 2
drawing	

