

## Bolt-down Fuseholders - Fuse Base for Fuse Strips Rated 80V

RoHS








### Specifications

|                              |                                                                                                                                                     |
|------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Base:</b>                 | Insulation material according to DIN 7708/1<br>Spring washer according ISO 4036<br>Hexagon nuts according to DIN 439<br>Washer according to DIN 125 |
| <b>Conducting materials:</b> | Copper wrought alloy / alliage cuivreux                                                                                                             |
| <b>Color:</b>                | Black / noir                                                                                                                                        |
| <b>Packaging unit:</b>       | 10 pieces                                                                                                                                           |

Fuse base for fuse strips with 62mm spacing. Up to 80V.

Sicherungshalter für Sicherungstreifen mit Stichmaß 62mm, bis 80V.

### Dimensions in mm / Maße in mm



| Part Number<br>Artikel-Nr. | Description<br>Beschreibung | Contact Temperature<br>Kontakttemperatur |
|----------------------------|-----------------------------|------------------------------------------|
| 177.5701.0001              | 1) Fuse base                | max. 425 A                               |
| 177.5731.0001              | 2) Fuse base                | max. 425 A                               |
| 192.5710.0001              | 3) Phase barrier            | —                                        |

Corresponding fuse strips see Section "Bolt-down Fuses."

**Bolt-down Fuseholders - Fuse Base for Fuse Strips Rated 80V**

RoHS






**Specifications**

- Base:**
- Insulation material according to DIN 7708/1  
Spring washer according ISO 4036  
Hexagon nuts according to DIN 439  
Washer according to DIN 125
- Conducting materials:**
- Copper wrought alloy / alliage cuivreux
- Color:**
- Black / noir
- Packaging unit:**
- 10 pieces

Fuse base for fuse strips with 62mm spacing. Up to 80V.

Sicherungshalter für Sicherungstreifen mit Stichmaß 62mm, bis 80V.

**Dimensions in mm / Maße in mm**



| Part Number<br>Artikel-Nr. | Description<br>Beschreibung | Contact Temperature<br>Kontakttemperatur |
|----------------------------|-----------------------------|------------------------------------------|
| 177.5702.0001              | 1) Fuse base                | max. 250 A                               |
| 177.5741.0001              | 2) Fuse base                | max. 250 A                               |
| 192.5710.0001              | 3) Phase barrier            | –                                        |

Corresponding fuse strips see Section “Bolt-down Fuses.”