


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
G	14				F	REV PER 0G3A-0363-01	10JUL01	JR/TM



AMP
WIRE RANGE

4 AWG
STRANDED

METRIC

DIMENSIONS LISTED IN mm [INCHES]

- NOTE:
- 1. STAMP AMP 4* LOCATE APPROX AS SHOWN
 - 2. TONGUE MATERIAL THK 1.22±0.08[.048±.003]
 - 3. WIRE INSULATION DIA 13.08[.515] MAX

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 150°c			100 QTY	LOOSE PC PACKAGE TYPE	53980-1 PART NO
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 600 V MAX	DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.20[.008] 3 PLC DEC ± - ANGLES ± -		DR 10-7-93 S.S. GOULDEN	AMP AMP Incorporated Harrisburg, PA 17105-3608	
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 16.77-26.65mm² [33,100-52,600] STRANDED	MATERIAL COPPER PER ASTM B-152 PVF², COLOR:NATURAL		CHK 10-7-93 R. HERSEY		
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		FINISH TIN/LEAD (93-7) PLATE ASTM B545	PRODUCT SPEC NOT AVAILABLE		NAME TERMINAL, RING TONGUE, PVF², PLASTI-GRIP, WIRE SIZE:4 AWG	
					APPLICATION SPEC NOT AVAILABLE	SIZE B	CAGE CODE 00779	DRAWING NO C-53980
					WEIGHT -	SCALE NTS	SHEET 1 OF 1	