


T-1 1/4 Wire Terminal


Part Number	Design Voltage	Amps	MSCP	Life Hours	Filament Type
CM2135	1.30	.030	.006	100	S-2
CM8631	1.35	.060	.006	500	C-2R
CM8655	2.50	.400	.550	30	C-2R
CM324	3.00	.190	.250	350	C-2R
CM7762	3.00	.030	.020	2,000	C-6
CM7778	3.00	.015	.003	10,000	C-6
CM515	5.00	.115	.150	40,000	C-2R
CM580	5.00	.060	.030	60,000	C-2R
CM583	5.00	.060	.050	25,000	C-2R
CM7761	5.00	.115	.150	2,000	C-6
CM7779	5.00	.060	.050	40,000	C-6
CM7780	5.00	.060	.030	10,000	C-6
CM8515	5.00	.115	.150	40,000	C-2R
CM634	6.00	.200	.630	1,000	C-2R
CM2114	6.00	.060	.130	3,000	C-2R
CM7760	6.00	.200	.600	2,000	C-6
CM7783	6.00	.060	.130	3,000	C-2V
CM7757	6.30	.200	.400	50,000	C-2V
CM7758	6.30	.075	.150	3,000	C-2V
CM7759	6.30	.040	.020	25,000	C-2V
CM7782	6.30	.200	.550	5,000	C-2V
CM8610	6.30	.200	.550	5,000	C-2R
CM7755	10.00	.040	.080	10,000	C-2F
CM7756	10.00	.015	.002	50,000	C-2F
CM7784	12.00	.040	.100	10,000	C-2F
CM7752	14.00	.080	.300	10,000	C-2F
CM7753	14.00	.080	.200	10,000	C-2F
CM7754	14.00	.065	.160	15,000	C-2F
CM7781	14.00	.080	.500	10,000	C-2F
CM8640	14.00	.080	.500	1,000	C-2F
CM7785	18.00	.040	.150	10,000	C-2F
CM7763	24.00	.050	.500	2,000	C-2F
CM7770	24.00	.035	.150	8,000	C-2F
CM7764	28.00	.024	.150	5,000	C-2F
CM7765	28.00	.025	.080	15,000	C-2F
CM7766	28.00	.040	.200	10,000	C-2F
CM7767	28.00	.040	.340	1,000	C-2F
CM7786	28.00	.040	.300	7,000	C-2F
CM8627	28.00	.040	.320	1,000	C-2F