

**Part Number: 92903-2210**

LaneLink™ / InfiniBand® Direct Attach Cable Assembly, 12X, 26AWG, Latches, 1.0m Length

Image not available

Status: **OBSOLETE**

Replacement: [929032230](#)


Series: [92903](#)

Category: Cable Assemblies

Series image - Reference only

Mates With Part(s):[91525](#)**Product Environmental Compliance**

EU RoHS: Not RoHS Compliant

China RoHS:  [China RoHS](#)

REACH SVHC: Not Reviewed

Low-Halogen Status: Not Reviewed

Part Detail**General**

Status	Obsolete
Category	Cable Assemblies
Series	92903
Connector to Connector	InfiniBand® 12x Both Ends
More Detailed Tech Information	LaneLink™ / InfiniBand® Direct Attach Cable Asse.0mbly, 12X, 26AWG, Latches, 1.0m
Obsolete Date	2004/11/01
Product Name	12X, InfiniBand®, LaneLink™

Physical

Cable Length	1.0m
Circuits (Loaded)	12X
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polyester, PVC
Packaging Type	Bag
Pitch - Mating Interface	0.50mm
Plating min - Mating	1.016µm
Plating min - Termination	3.048µm
Single Ended	No
Termination Interface: Style	Surface Mount
Wire Size AWG	26
Wire/Cable Type	Parallel Pair

Electrical**(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	0.5A
Impedance	100Ω
Shielded	Yes
Voltage - Maximum	30V AC

Material Info

UPC	756054811764
-----	--------------

Reference - Drawing Numbers

Packaging Specification	PK-92903-001
Product Specification	PS-91525-001
Sales Drawing	SD-92903-001

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling

Specification document.

**Previously Available Application
Tooling**

[Check our list of old tooling that used to be
available for this part](#)