

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

38700-6330

Status:


Active

Overview:

Beau™ Barrier Strips

Description:

8.26mm Pitch Beau™ PCB Terminal Strip, without Mounting Ends, 30 Circuits



Series

image - Reference only

Documents:

- [3D Model](#)
- [Drawing \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

General

|                |                      |
|----------------|----------------------|
| Product Family | Terminal Blocks      |
| Series         | 38700                |
| Application    | N/A                  |
| Component Type | One Piece            |
| Overview       | Beau™ Barrier Strips |
| Product Name   | Fixed Mount Barrier  |
| Type           | Barrier Strip        |
| UPC            | 800756314556         |

Physical

|                                |                    |
|--------------------------------|--------------------|
| Circuits (Loaded)              | 30                 |
| Circuits (maximum)             | 30                 |
| Color - Resin                  | Black              |
| Entry Angle                    | Horizontal         |
| Lock to Mating Part            | None               |
| Material - Metal               | Brass              |
| Material - Plating Mating      | Tin                |
| Material - Plating Termination | Tin                |
| Material - Resin               | Polyester          |
| Number of Rows                 | 1                  |
| Orientation                    | Horizontal         |
| PC Tail Length                 | 3.56mm             |
| PCB Retention                  | None               |
| Panel Mount                    | No                 |
| Pitch - Mating Interface       | 8.26mm             |
| Pitch - Termination Interface  | 8.26mm             |
| Plating min - Mating           | 3.810µm            |
| Plating min - Termination      | 3.810µm            |
| Polarized to Mating Part       | No                 |
| Shrouded                       | Dual-Barrier       |
| Stackable                      | Yes                |
| Surface Mount Compatible (SMC) | No                 |
| Temperature Range - Operating  | -40°C to +130°C    |
| Termination Interface: Style   | Through Hole       |
| Wire Size AWG                  | 14, 16, 18, 20, 22 |
| Wire Size mm²                  | 0.50 - 1.50        |

Electrical

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 15A  |
| Voltage - Maximum             | 300V |

Material Info

|                 |         |
|-----------------|---------|
| Old Part Number | 70530-C |
|-----------------|---------|

Reference - Drawing Numbers

|               |              |
|---------------|--------------|
| Sales Drawing | SD-38700-001 |
|---------------|--------------|

EU RoHS

ELV and RoHS  
Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product  
environmental compliance?

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of  
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any  
non-product compliance questions.

Search Parts in this Series

38700Series

Mates With

N/A

This document was generated on 10/14/2014

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

38700-6330