

Search within category

GO

BUY NOW

DESIGN / INSTALL



VB1B1L2BN12J1

The 30A, 208V vertical power strip in black has 12 NEMA L6-20R receptacles. It features two 20A double-pole magnetic breaker on-off switches with integral switch guard, a red LED current monitor, and a 10' (3m) power cord with a NEMA L6-30P twist-lock plug. It is UL and c-UL listed and measures 66.3H x 2.0W x 2.0D (1683mm x 51mm x 51mm). The breaker doghouse adds 1.44 (87.4mm) to the overall depth. It is sold individually.

|                                |                                 |           |                    |              |
|--------------------------------|---------------------------------|-----------|--------------------|--------------|
| Specs                          | Packaging Details               | Documents | ★ Add to Favorites | 🛒 Add to BOM |
| Rack PDU Type                  | Basic Rack PDU with Local Meter |           |                    |              |
| Monitoring                     | Local Meter                     |           |                    |              |
| Remote Outlet Switching        | No                              |           |                    |              |
| Mount Orientation              | Vertical                        |           |                    |              |
| Current Rating (Amps)          | 30A                             |           |                    |              |
| Input Voltage                  | 208V - Single Phase             |           |                    |              |
| Plug Type                      | NEMA L6-30P                     |           |                    |              |
| Output Voltage                 | 208V                            |           |                    |              |
| Receptacle Type                | NEMA L6-20R                     |           |                    |              |
| Total Number of Outlets        | 12                              |           |                    |              |
| Depth (In.)                    | 2.00                            |           |                    |              |
| Depth (mm)                     | 50.8                            |           |                    |              |
| Height (In.)                   | 66.25                           |           |                    |              |
| Height (mm)                    | 1682.8                          |           |                    |              |
| Width (In.)                    | 2.00                            |           |                    |              |
| Width (mm)                     | 50.8                            |           |                    |              |
| Tool-Less Button Spacing (In.) | 64.75                           |           |                    |              |
| Tool-Less Button Spacing (mm)  | 1644.7                          |           |                    |              |
| No. of Rack Spaces             | 0                               |           |                    |              |
| Surge Suppression              | No                              |           |                    |              |
| Amps                           | 30A                             |           |                    |              |
| Cable Length                   | 3                               |           |                    |              |
| Length (In.)                   | 71.50                           |           |                    |              |
| UL Recognized                  | Yes                             |           |                    |              |
| Voltage                        | 208V                            |           |                    |              |
| RoHS Compliancy Status         | Compliant                       |           |                    |              |
| Min. Order Qty.                | 1                               |           |                    |              |