






MATERIAL NUMBER	OLD PART NUMBER
1201140034	BTY4□30-F BA



WIRING DIAGRAM

VOLTAGE RATING	10-30 VDC
AMPERAGE RATING PER PORT	4 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	-20°C TO 90°C

ITEM	COMPONENT	MATERIAL	FINISH
1	INSERT	PBT	YELLOW
2	CONTACT SOCKET	COPPER ALLOY	GOLD OVER NICKEL
3	O-RING	VITON	RED
4	RECEPTACLE SHELL	BRASS	NICKEL PLATED
5	HOUSING	PBT	YELLOW
6	LABEL	ABS	WHITE

RLSD DRAWING EC NO: WEL2010-0374 DRWN: FPAHER 2010/02/16 CHKD: NS APPR: NSTAUDIG 2010/02/18	DESCRIPTION EV	QUALITY SYMBOL  = 0  = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM		SCALE ----	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION 			
				mm	INCH	DRAWN BY BW	DATE 2009/04/03	TITLE MICRO-CHANGE MPIS 4 PORT TOP MOUNT TWIN I/O ATTACHABLE					
			4 PLACES	±-	±-	CHECKED BY TW	DATE 2009/04/03						
			3 PLACES	±-	±-	APPROVED BY NSTAUDIG		DATE 2010/02/18		 MOLEX INCORPORATED			
			2 PLACES	±-	±.01								
			1 PLACE	±0.3	±-	MATERIAL NO. SEE CHART				DOCUMENT NO. SD-120114-012		SHEET NO. 1 OF 1	
			ANGULAR ±°										
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS													