



1 TIP 1 ————— BLACK
 RING
 2 TIP ————— RED
 RING

SCHEMATIC

FEATURES:

- Shielded cable to reduce noise.
- Wired for long pins looking out to field
- Dual Bantam Plugs are molded to the cable for optimum durability

MATERIALS:

Plug – Dual Bantam, nickel plated brass

Cable – 4 Conductor shielded twisted pair

RATINGS:

Operating Temperature: -20°C to +80°C

Operating Voltage: 300 VRMS Max.

Current: 3.36 Amperes @ 25°C Max.

Nominal capacitance conductor to shield: 720pf

Nominal capacitance between conductors pairs: 420pf

ORDERING INFORMATION: Model 6329-96

Standard Length – 96 Inches (2134 mm)

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02"$ (.51 mm), .xxx = $\pm .005"$ (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA