

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301050035](#)
Status: **Active**
Overview: [Specialty Lighting](#)
Description: Watertite Wet Location 35W 12V Flood Light with In-line Transformer, Screw Release Guard, 14/2 SOOW, Overall Length 7.62m (50.0')

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
Series [130105](#)
NEMA Configuration NEMA 5-15
NEMA Rating NEMA 4X
Outlet None
Overview [Specialty Lighting](#)
Product Name Watertite
Type Hand Lamps, Specialty Light
UPC 78678861532

Physical

Cord Length - Primary 3.04m (10.0')
Cord Length - Secondary 15.24m (50.0')
Depth N/A
Duty Wet Location
Guard Included Yes
Guard Type Screw Release
Height 127.00mm (5.000")
Length 228.60mm (9.000")
Material - Guard #10 Gauge Vinyl Coated Steel
Mounting Style Hand Held
Packaging Type Carton
Socket Construction N/A

Electrical

Bulb Type Quartz Halogen
Cord Type - Primary 16/3 SOOW
Cord Type - Secondary 14/2 SOOW
Lamp Type PAR36
Lamp Wattage - Maximum 35W
Lumens 350
On/Off Switch No
Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Engineering Number 1612



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130105](#) Series