

[support](#) | [locate distributor](#) | [about panduit](#) | [careers](#) | [worldwide](#)*World Leader in Network and Electrical Solutions*[Printer Friendly](#)[HOME](#) | [SOLUTIONS](#) | [RESOURCES](#) | [PRODUCTS](#) | [SERVICES](#) | [LEARNING](#)SEARCH Current refinements (click ☒ to remove)☒ [Region](#) ▶ [USA](#) ☒ [Product Family](#) ▶ [HSTT Heat Shrink 4 ft. Pieces](#) ☒ [Text Search: 'HSTT38-48-QC'](#)[Search Tips](#) **Your search criteria matched only one product, shown below.**

- Shrink ratio of 2:1 insulates a wide range of diameters and irregular shapes
- Cross-linked, UV resistant material improves flame retardancy, chemical, and temperature resistance

For clear, add "C" to end of part number package suffix (Example HSTT05-48-QC). Contact customer service for additional color information.

^ Meets Mil Spec AMS-DTL-23053/5 Class 1(Colors), Class 2 (Clear)

|                                         |                                                       |
|-----------------------------------------|-------------------------------------------------------|
| Part Number:                            | HSTT38-48-QC                                          |
| RoHS Compliancy Status:                 | Compliant                                             |
| Part Description:                       | Thin Wall Polyolefin Heat Shrink                      |
| Material:                               | Flame retardant polyolefin cross-linked except clear^ |
| Color:                                  | Clear                                                 |
| Military Specification:                 | AMS-DTL-23053/5 Class 2                               |
| Length (ft.):                           | 4                                                     |
| Length (m):                             | 1.2                                                   |
| Max. Recovered I.D. (In.):              | .187                                                  |
| Max. Recovered I.D. (mm):               | 4.8                                                   |
| Min. Expanded I.D. (In.):               | .375                                                  |
| Min. Expanded I.D. (mm):                | 9.5                                                   |
| Nominal Diameter / Size:                | 3/8                                                   |
| Nominal Recovered Wall Thickness (In.): | .025                                                  |
| Nominal Recovered Wall Thickness (mm):  | .6                                                    |
| Shrink Ratio:                           | 2:1                                                   |
| Temperature Range:                      | -67°F to 275°F (-55°C to 135°C)                       |
| Min. Order UOM:                         | PC                                                    |
| Min. Order Qty.:                        | 25                                                    |
| BOM Qty. (# of Pkgs.)                   | <input type="text" value="0"/>                        |
| Add to My Catalog                       | <input type="checkbox"/>                              |

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.

[View Content Details](#)[Evaluate](#)[Design a Solution](#)[Install & Maintain](#)**Installation Instructions:**[Pan-Shrink Heat Shrink - In001 pdf](#)[legal information](#) | [privacy policy](#) | [site map](#)

Copyright © 1995-2007, PANDUIT CORP. All rights reserved.