

LC1D50U7

CONTACTOR 600VAC 50AMP IEC +OPTIONS

List Price \$293.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

Technical Characteristics

Contacteur Type	Non-Reversing
Inductive Amperes (AC3)	50A
Resistive Amperes (AC1)	80A
Certifications	UL Listed (E164862 / NLDX) - CSA Certified (LR43364 3211 04) - IEC Rated (60647-4) - CE Marked - RoHS Compliant
Marketing Trade Name	TeSys
Horsepower Rating (1-Phase)	3HP@115Vac - 7.5HP@230Vac
Horsepower Rating (3-Phase)	15HP@200/230Vac - 40HP@460/575Vac
Maximum Voltage Rating	600 Vac
Number of Poles	3-Pole (3 NO)
Coil Voltage	240Vac@50/60Hz
Terminal Type	Screw Clamp
Type	TeSys D

Shipping and Ordering

Category	22345 -
Discount Schedule	I12
GTIN	00785901207641
Package Quantity	1
Weight	3.12 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	CZ

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.