


Dimensions (In.)**Specifications:**

- Tube material: hard glass
- Wall thickness: .9mm
- Type of gas: xenon
- Internal gas pressure: 150mm Hg
- Anode to cathode voltage (V): 220 min. 360 nom. 400 max.
- Max. energy per flash: 60 ws
- Flashes with max. energy input: max. flash rate 6/minute
Nominal life: 5000 flashes
- Trigger: 4KV min. voltage .6mws min. input
- Applications: photographic

Your source for quality electronics. Toll-free full service
(800) 346-6873

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xicon:

36FT050