

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300540013](#)
Status: **Active**
Overview: [Brad Industrial Ethernet Solutions](#)
Description: Ultra-Lock (M12) Single-Ended Receptacle, 4 Poles, Female (Straight) to Pigtail, 2.0m (6.56') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E200650

General

Product Family Industrial Cordsets
Series [130054](#)
Connector End A Ultra-Lock (M12)
Connector End B Pigtail
IP Rating IP67
Material - Contact Copper Alloy
Overview [Brad Industrial Ethernet Solutions](#)
Performance Category 5e
Product Name Ultra-Lock (M12)
Protocol N/A
Type Single Ended
UPC 78678804778

Physical

Cable Diameter N/A
Cable Length 2.0m (6.56')
Color - Cable Jacket Teal
Coupling Style Threaded
Gender Female-Pigtail
Keyway D-coded
LED Indicator No
Material - Cable Jacket PVC
Material - Connector Body PVC
Material - Coupling Nut Nickel-plated Brass
Material - Plating Mating Gold
Orientation Straight to Pigtail
Poles 4
Temperature Range - Operating -25°C to +75°C
Wire Size AWG 24
Wire/Cable Type E152210

Electrical


Current - Maximum per Contact 1.5A
Voltage - Maximum 125V

Material Info

Engineering Number ERWAAJ4002M020

Reference - Drawing Numbers

Sales Drawing SD-130054-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per -
D(2020)4578-DC (25
June 2020)
Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[130054](#) Series