








NOTE:

1. MATERIAL:
HOUSING: HIGH TEMP. THERMOPLASTIC, UL 94V-0, COLOR: NATURAL.
CONTACTS: PHOSPHOR BRONZE.
TAB: PHOSPHOR BRONZE.
2. FINISH:
CONTACTS: (SEE TABLE) OVER 50μ" MIN. NICKEL PLATED.
TAB: 100μ" MIN. MATTE-TIN OVER 50μ" MIN. NICKEL PLATED.
3. NO TYCO LOGO AND DATE CODE ON THE PRODUCT.
4. LOCKING WINDOW:
ONE PLACE FOR 2 AND 3 CONTACTS,
TWO PLACES FOR MORE THAN 3 CONTACTS.
5. RECOMMENDED PART NUMBER OF CABLE ASSEMBLY:
HOUSING: X-440146-X
CONTACT: 440147-X


A1		REVISED PER ECO-11-005301	RK HMR	02APR15
LTR	REVISION RECORD	ECO	DWN CHK	DATE



RECOMMENDED PC BOARD LAYOUT
(TOLERANCE: ± 0.05)



2 CONTACTS




3 CONTACTS


0.762μm [30μ"] MIN. GOLD	17.50	19.30	20.50	24.04	15	4-1734261-5
	16.25	18.05	19.25	22.79	14	4-1734261-4
	15.00	16.80	18.00	21.54	13	4-1734261-3
	13.75	15.55	16.75	20.29	12	4-1734261-2
	12.50	14.30	15.50	19.04	11	4-1734261-1
	11.25	13.05	14.25	17.79	10	4-1734261-0
	10.00	11.80	13.00	16.54	9	3-1734261-9
	8.75	10.55	11.75	15.29	8	3-1734261-8
	7.50	9.30	10.50	14.04	7	3-1734261-7
	6.25	8.05	9.25	12.79	6	3-1734261-6
	5.00	6.80	8.00	11.54	5	3-1734261-5
	3.75	5.55	6.75	10.29	4	3-1734261-4
2.54μm [100μ"] MIN. MATTE-TIN	2.50	4.30	5.50	9.04	3	3-1734261-3
	1.25	3.05	4.25	7.79	2	3-1734261-2
	17.50	19.30	20.50	24.04	15	1-1734261-5
	16.25	18.05	19.25	22.79	14	1-1734261-4
	15.00	16.80	18.00	21.54	13	1-1734261-3
	13.75	15.55	16.75	20.29	12	1-1734261-2
	12.50	14.30	15.50	19.04	11	1-1734261-1
	11.25	13.05	14.25	17.79	10	1-1734261-0
	10.00	11.80	13.00	16.54	9	1734261-9
	8.75	10.55	11.75	15.29	8	1734261-8
	7.50	9.30	10.50	14.04	7	1734261-7
	6.25	8.05	9.25	12.79	6	1734261-6
CONTACT PLATING	5.00	6.80	8.00	11.54	5	1734261-5
	3.75	5.55	6.75	10.29	4	1734261-4
	2.50	4.30	5.50	9.04	3	1734261-3
	1.25	3.05	4.25	7.79	2	1734261-2
	D	C	B	A	NO. OF CONTACTS	PART NUMBER
	DIMENSION					

TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.38 2 PLC ±0.25 3 PLC ±- ANGLES ±3°		DWN A. WU 02-DEC-2005		 TE Connectivity			
		CHK S. HOU 02-DEC-2005					
MATERIAL		APVD W.J. KE 02-DEC-2005		WIRE TO BOARD MALE HEADER, 1.25 MM PITCH, SMT, RIGHT ANGLE TYPE			
SEE NOTE		PRODUCT SPEC 108-57273					
FINISH		QUALIFICATION TEST REPORT 501-57299		LOC DW	SIZE A ₃	DRAWING NO C-1734261	REV A1
SEE NOTE		WEIGHT -		SCALE --		SHEET 1 OF 2	

DIST	QUANTITY	PCS/ REEL	REELS/ CARTON	DIM. W	15
					14
8	4000	1000	4	44.0	13
					12
					11
					10
7	6000	1000	6	32.0	9
					8
					7
					6
6	7000	1000	7	24.0	5
					4
					3
					2
5	10000	1000	10	16.0	NO. OF CONTACTS



NOTE:
1. CARTON DIMENSIONS: 340 X 340 X 250



TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- ANGLES ±-	DWN A. WU 02-DEC-2005	TE Connectivity			
	CHK S. HOU 02-DEC-2005				
	APVD W.J. KE 02-DEC-2005	NAME WIRE TO BOARD MALE HEADER, 1.25 MM PITCH, SMT, RIGHT ANGLE TYPE			
	PRODUCT SPEC -				
MATERIAL -	APPLICATION SPEC -	LOC DW	SIZE A ₃	DRAWING NO C-1734261	REV A1
FINISH -	WEIGHT -	SCALE --	SHEET 2 OF 2		

LTR	REVISION RECORD	SEE SHEET 1.	ECO	DWN CHK	DATE