



MASTER TL-D 90 De Luxe

MASTER TL-D 90 De Luxe 36W/965 1SL

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Product data

• General Characteristics

Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Bulb	T8 [26 mm]
Life to 10% failures EM	12000 hr
Life to 10% fail Preheat EL,3h	17000 hr
Life to 10% fail Nonpreh EL,3h	10000 hr
Life to 50% failures EM	15000 hr
Life to 50% fail Preheat EL,3h	20000 hr
Life to 50% fail Nonpreh EL,3h	12000 hr
LSF EM 2000h Rated, 3h cycle	99 %
LSF EM 4000h Rated, 3h cycle	99 %
LSF EM 6000h Rated, 3h cycle	99 %
LSF EM 8000h Rated, 3h cycle	99 %
LSF EM 12000h Rated,3h cycle	89 %
LSF EM 16000h Rated,3h cycle	33 %
LSF EM 20000h Rated,3h cycle	2 %

• Light Technical Characteristics

Colour Code	965 [CCT of 6500K]
Colour Rendering Index	93 Ra8
Colour Designation	Cool Daylight
Colour Temperature	6500 K

Luminous Flux EM 25°C, Rated	2800 Lm
Luminous Flux EM 25°C, Nominal	2800 Lm
Lum Efficacy Rated EM 25°C	77.8 Lm/W
Average Luminance EM	1.00 cd/cm2
LLMF EM 2000h Rated	96 %
LLMF EM 4000h Rated	95 %
LLMF EM 6000h Rated	94 %
LLMF EM 8000h Rated	93 %
LLMF EM 12000h Rated	92 %
LLMF EM 16000h Rated	91 %
LLMF EM 20000h Rated	90 %
Design Temperature	25 C
Chromaticity Coordinate X	309 -
Chromaticity Coordinate Y	322 -

• Electrical Characteristics

Lamp Wattage	36 W
Lamp Wattage EM 25°C, Nominal	36 W
Lamp Wattage EM 25°C, Rated	36.0 W
Lamp Voltage EM 25°C	103 V



asimpleswitch.com

PHILIPS

MASTER TL-D 90 De Luxe

Lamp Current EM 0.440 A
25°C
Dimmable yes

• Environmental Characteristics

Energy Efficiency A
Label (EEL)
Mercury (Hg) 3.0 mg
Content
Energy consumption 43 kWh
kWh/1000h



• Product Dimensions

Base Face to Base 1199.4 (max) mm
Face A
Insertion Length B 1204.1 (min), 1206.5 (max) mm
Overall Length C 1213.6 (max) mm
Diameter D 28 (max) mm

• Product Data

Order code 888624 25
Full product code 871150088862425
Full product name MASTER TL-D 90 De Luxe 36W/965 1SL
Order product name MASTER TL-D 90 De Luxe 36W/965 1SL/10
Pieces per pack 1
Packing configuration 10
Packs per outerbox 10
Bar code on pack - EAN1 8711500888624
Bar code on outerbox - EAN3 8711500888631
Logistic code(s) - 12NC 928044596581
ILCOS code FD-36/65/1A-E-G13
Net weight per piece 137.500 gr

Dimensional drawing





G13

MASTER TL-D 90 De Luxe 36W/965 1SL

Product	A (Max)	B (Min)	B (Max)	C (Max)	D (Max)
TL-D De Luxe 36W/965	1199.4	1204.1	1206.5	1213.6	28

Photometric data





© 2013 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2013, July 4
data subject to change