

1

2


3

4

Double row strip socket pitch 2.54mm

A


A



B

B

PCB Layout



C

C

RoHS
Compliant

PIN: Brass, Machined, CuZn38Pb2
Plating: 2um/80u" nickel, 5um/200" TIN
Plating Inner Contact: 2um/80u" nickel, Gold
Insulator: Polyamide, glass filled, UL94V-0
Current Rating: 3A/Contact max.
Contact Resistance: <4mOhm/Contact
Insulation Resistance: >1000Mohm at V=100V
Operating: 60Vac/DC
Operating Temperature: -40°C to +105°C
Soldering Temperature: 260°C 10's max

Contact	DIM A	DIM B
10	12.70	10.16
14	17.78	15.24
16	20.32	17.78
20	25.40	22.86
26	33.02	30.48
32	40.64	38.10
34	43.18	40.64
40	50.80	48.26
50	63.50	60.96
60	76.20	73.66
64	81.28	78.74

Description

Name: **AWD127/xx/Z-T**
Female socket w/machined
pins, double row

ASSMANN
Electronic Components

1

2

3

4

D

D

THIS DRAWING IS UNPUBLISHED

© Copyright 2005 by Assmann Electronic Components All International Rights Reserved

This drawing is a controlled document for Assmann Electronics, Inc. It is subject to change and the controlling engineering organization should be contacted for the latest revision.