



Search Results

- Evaluate
- [FAQ's](#)
- Design a Solution
- [Part Drawings](#)
 - [DWG-Mini-Com Min ..](#)
 - [PDFMini-Com Min ..](#)
 - [DXF-Mini-Com Min ..](#)
- How to Buy
- [Bill of Material](#)
 - [Favorite Products List](#)
 - [Locate Distributor](#)
- Install & Maintain
- [Installation Instructions](#)
 - [PDFMini-Com Min ..](#)

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click to remove) [Search Tips](#) [Within Results](#)

Text Search: 'CJ66IW'

Your search criteria matched only one product, shown below

CJ66IWY



- Patented lead frame termination style ensures twists are maintained to within 1/2"
- No punchdown tool required, optional termination tool (CJT -X) ensures conductors are fully terminated
- Termination cap provides excellent strain relief; helps control cable bend radius and securely retains wires
- Clear, removable termination cap provides easy troubleshooting
- Terminate 4 -pair 24 and 22 AWG 100 ohm solid unshielded twisted pair cable
- Accept 6 and 8-position modular plugs without damage
- White colored module base designates Category 3 performance
- Can be clearly identified with optional labels and icons
- Compatible with *Mini-Com*® Modular Patch Panels, Faceplates, and Surface Mount Boxes

Part Number	CJ66IWY
RoHS Compliancy Status	Compliant
Note	CJ66IWY replaces CJ66IW
Part Description	Category 3, 6-position, 6-wire universal module.
Product Type	Copper Jack Module
Color	Off White
Modular Jack Type	RJ11
No. of Module Spaces	1
Performance Level	Category 3
Pricing Description	Mini-Com MiniJack Module, Cat 3, UTP, 6 pos 6 wire, Universal, Off White
Wiring Scheme	T568A/T568B
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.