







Accessories

Identification	No. of contacts	Part No.	Drawing	Dimensions in mm																														
Dust cap black thermoplastic for male connector	9 15 25 37	09 67 009 0611 09 67 015 0611 09 67 025 0611 09 67 037 0611		<table><tr><th></th><th>A</th><th>B</th></tr><tr><td>9</td><td>17.0</td><td>22.40</td></tr><tr><td>15</td><td>25.3</td><td>30.80</td></tr><tr><td>25</td><td>38.9</td><td>44.40</td></tr><tr><td>37</td><td>55.4</td><td>60.75</td></tr></table>		A	B	9	17.0	22.40	15	25.3	30.80	25	38.9	44.40	37	55.4	60.75															
	A	B																																
9	17.0	22.40																																
15	25.3	30.80																																
25	38.9	44.40																																
37	55.4	60.75																																
for female connector	9 15 25 37	09 67 009 0711 09 67 015 0711 09 67 025 0711 09 67 037 0711		<table><tr><th></th><th>A</th><th>B</th></tr><tr><td>9</td><td>16.0</td><td>22.5</td></tr><tr><td>15</td><td>24.4</td><td>31.0</td></tr><tr><td>25</td><td>37.8</td><td>44.3</td></tr><tr><td>37</td><td>54.3</td><td>60.8</td></tr></table>		A	B	9	16.0	22.5	15	24.4	31.0	25	37.8	44.3	37	54.3	60.8															
	A	B																																
9	16.0	22.5																																
15	24.4	31.0																																
25	37.8	44.3																																
37	54.3	60.8																																
antistatic black thermoplastic for male connector	9 15 25 37 50	09 67 009 0612 09 67 015 0612 09 67 025 0612 09 67 037 0612 09 67 050 0612		<table><tr><th></th><th>A</th><th>B</th><th>C</th><th>D</th></tr><tr><td>9</td><td>17.7</td><td>21.8</td><td>13.2</td><td>9.1</td></tr><tr><td>15</td><td>26.0</td><td>30.0</td><td>13.2</td><td>9.1</td></tr><tr><td>25</td><td>40.0</td><td>44.2</td><td>13.2</td><td>9.1</td></tr><tr><td>37</td><td>56.4</td><td>59.8</td><td>13.2</td><td>9.1</td></tr><tr><td>50</td><td>53.9</td><td>57.8</td><td>15.9</td><td>11.7</td></tr></table>		A	B	C	D	9	17.7	21.8	13.2	9.1	15	26.0	30.0	13.2	9.1	25	40.0	44.2	13.2	9.1	37	56.4	59.8	13.2	9.1	50	53.9	57.8	15.9	11.7
	A	B	C	D																														
9	17.7	21.8	13.2	9.1																														
15	26.0	30.0	13.2	9.1																														
25	40.0	44.2	13.2	9.1																														
37	56.4	59.8	13.2	9.1																														
50	53.9	57.8	15.9	11.7																														
for female connector	9 15 25 37 50	09 67 009 0712 09 67 015 0712 09 67 025 0712 09 67 037 0712 09 67 050 0712		<table><tr><th></th><th>A</th><th>B</th><th>C</th><th>D</th></tr><tr><td>9</td><td>15.9</td><td>20.0</td><td>11.8</td><td>7.8</td></tr><tr><td>15</td><td>24.4</td><td>28.5</td><td>11.8</td><td>7.8</td></tr><tr><td>25</td><td>38.3</td><td>42.3</td><td>11.8</td><td>7.8</td></tr><tr><td>37</td><td>54.7</td><td>58.8</td><td>11.8</td><td>7.8</td></tr><tr><td>50</td><td>52.6</td><td>56.2</td><td>14.5</td><td>10.5</td></tr></table>		A	B	C	D	9	15.9	20.0	11.8	7.8	15	24.4	28.5	11.8	7.8	25	38.3	42.3	11.8	7.8	37	54.7	58.8	11.8	7.8	50	52.6	56.2	14.5	10.5
	A	B	C	D																														
9	15.9	20.0	11.8	7.8																														
15	24.4	28.5	11.8	7.8																														
25	38.3	42.3	11.8	7.8																														
37	54.7	58.8	11.8	7.8																														
50	52.6	56.2	14.5	10.5																														
UL 94 V0 grey thermoplastic for male connector	9 15 25 37 50	09 67 009 0613 09 67 015 0613 09 67 025 0613 09 67 037 0613 09 67 050 0613		<table><tr><th></th><th>A</th><th>B</th><th>C</th><th>D</th></tr><tr><td>9</td><td>17.7</td><td>21.8</td><td>13.2</td><td>9.1</td></tr><tr><td>15</td><td>26.0</td><td>30.0</td><td>13.2</td><td>9.1</td></tr><tr><td>25</td><td>40.0</td><td>44.2</td><td>13.2</td><td>9.1</td></tr><tr><td>37</td><td>56.4</td><td>59.8</td><td>13.2</td><td>9.1</td></tr><tr><td>50</td><td>53.9</td><td>57.8</td><td>15.9</td><td>11.7</td></tr></table>		A	B	C	D	9	17.7	21.8	13.2	9.1	15	26.0	30.0	13.2	9.1	25	40.0	44.2	13.2	9.1	37	56.4	59.8	13.2	9.1	50	53.9	57.8	15.9	11.7
	A	B	C	D																														
9	17.7	21.8	13.2	9.1																														
15	26.0	30.0	13.2	9.1																														
25	40.0	44.2	13.2	9.1																														
37	56.4	59.8	13.2	9.1																														
50	53.9	57.8	15.9	11.7																														
for female connector	9 15 25 37 50	09 67 009 0713 09 67 015 0713 09 67 025 0713 09 67 037 0713 09 67 050 0713		<table><tr><th></th><th>A</th><th>B</th><th>C</th><th>D</th></tr><tr><td>9</td><td>15.9</td><td>20.0</td><td>11.8</td><td>7.8</td></tr><tr><td>15</td><td>24.4</td><td>28.5</td><td>11.8</td><td>7.8</td></tr><tr><td>25</td><td>38.3</td><td>42.3</td><td>11.8</td><td>7.8</td></tr><tr><td>37</td><td>54.7</td><td>58.8</td><td>11.8</td><td>7.8</td></tr><tr><td>50</td><td>52.6</td><td>56.2</td><td>14.5</td><td>10.5</td></tr></table>		A	B	C	D	9	15.9	20.0	11.8	7.8	15	24.4	28.5	11.8	7.8	25	38.3	42.3	11.8	7.8	37	54.7	58.8	11.8	7.8	50	52.6	56.2	14.5	10.5
	A	B	C	D																														
9	15.9	20.0	11.8	7.8																														
15	24.4	28.5	11.8	7.8																														
25	38.3	42.3	11.8	7.8																														
37	54.7	58.8	11.8	7.8																														
50	52.6	56.2	14.5	10.5																														