

► Heatsinks f.cool

► Cases f.case

▼ Connectors f.con

▼ Sockets

- High-precision sockets and plugs for DIL-IC
- Sockets for IC-PLCC
- Sockets for TO ... cases
- Sockets for crystal oscillators
- Jumper links / Separable jumpers
- High-precision contacts, loose
- Connector-sleeves

► PCB connectors

► IDC-connectors

► D-Sub connectors

■ Brackets for PC

► Optoelectronics

High-precision contacts, loose

SK 40 ...

SK 40 G

pin contacts

Data sheet

add to request



Features

Technical Drawing

Service

contact material	CuZn-alloy
surface contact /	Ni+≥0.2µm Au
contact sleeve	Ni+4...6µm Sn
type	male
nominal current	1.5 A
nominal voltage	60 V DC
test voltage	1000 V
surface of contact	gold-plated
connection type	-
grid	2.54 mm