




224K012-3-0 Product Details

[Share](#) [Print](#) [Email](#)


224K012-3-0

TE Internal Number: 822255-000

Active

Molded Parts

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Molded Part Type = Molded Boot
- Family Name = 224K0
- Straight
- General Purpose Application
- Entry Size, Braided or Magneform Adapter = 6, 7

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)
[Request Sample](#)
[Find Similar Products](#)
[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [Boot, 90 deg., With Lip \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Molded Part Type](#) = Molded Boot
- [Family Name](#) = 224K0
- [Angle](#) = Straight
- [Adhesive Description](#) = Adhesive Purchased Separately.
- [Size](#) = 12

Mechanical Attachment:

- [Adhesive Pre-Coating](#) = Without

Dimensions:

- [Adapter Entry Size Outside Diameter \(Min-Max\) \(mm \[in\]\)](#) = 14.00 - 18.00 [0.551 - 0.709]
- [Cable Diameter Range \(mm \[in\]\)](#) = 3.30 - 8.00 [0.130 - 0.315]

Body Features:

- [Material](#) = Semi rigid Modified Polyolefin

Housing Features:

- [Entry Size, Braided or Magneform Adapter](#) = 6, 7
- [Entry Size, Tinel-Lock Adapter](#) = 5, 6
- [Entry Size - Spin Coupling Adapter](#) = 6 - 7
- [Material Systems Code](#) = 10

Configuration Features:

- [Material Code](#) = 3

Industry Standards:

- [Government/Industry Qualification](#) = No
- [Approved Standards](#) = DEF Std 59-97 Issue 3 Type DA, MIL-I-81765/1 Class I, UL224 E85831
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

Environmental:

- [Operating Temperature \(°C\)](#) = -55 - +135

Operation/Application:

- [Application](#) = General Purpose

Purchasing Information:

- [Adhesive Code](#) = S1125

Other:

- [Brand](#) = Raychem
- [Comment](#) = Contact Raychem for additional adhesive and/or cut off boot length information

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

