


PANDUIT PART #	WIRE RANGE		COLOR*	WIRE STRIP LENGTH +1/32 -0 [+0.8 -0]	MAX. WIRE INSUL. DIA.	DIMENSIONS in. [mm]					INSTALLATION TOOLS
	AWG	[mm ²]				L	P	ID-1	S1	S2	
FSD72-6	26	[0,14]	GRAY	3/8 [9,5]	0.07 [2,0]	.41 [10,5]	.24 [6,0]	0.03 [0,8]	[0,15]	[0,25]	CT-1002 CT-1123
FSD72-8				15/32 [11,9]	0.07 [2,0]	0.49 [12,5]	0.31 [8,0]	0.03 [0,8]	[0,15]	[0,25]	
FSD73-6	24	[0,25]	YELLOW	3/8 [9,5]	0.07 [2,0]	.41 [10,5]	.24 [6,0]	0.03 [0,8]	[0,15]	[0,25]	
FSD73-8				15/32 [11,9]	0.07 [2,0]	0.49 [12,5]	0.31 [8,0]	0.03 [0,8]	[0,15]	[0,25]	
FSD74-6	24-22	[0,34]	TURQUOISE	3/8 [9,5]	0.07 [2,0]	.41 [10,5]	.24 [6,0]	0.03 [0,8]	[0,15]	[0,25]	
FSD74-8				15/32 [11,9]	0.07 [2,0]	0.49 [12,5]	0.31 [8,0]	0.03 [0,8]	[0,15]	[0,25]	
FSD75-6	22-20	[0,50]	WHITE	3/8 [9,5]	0.09 [2,5]	0.45 [11,5]	0.24 [6,0]	0.04 [1,1]	[0,15]	[0,25]	
FSD75-8				15/32 [11,9]	0.09 [2,5]	0.53 [13,5]	0.31 [8,0]	0.04 [1,1]	[0,15]	[0,25]	
FSD75-10				17/32 [13,5]	0.09 [2,5]	0.61 [15,5]	0.39 [10,0]	0.04 [1,1]	[0,15]	[0,25]	
FSD76-6	18	[0,75]	GRAY	3/8 [9,5]	0.11 [2,8]	0.47 [12,0]	0.24 [6,0]	0.05 [1,3]	[0,15]	[0,25]	
FSD76-8				15/32 [11,9]	0.11 [2,8]	0.55 [14,0]	0.31 [8,0]	0.05 [1,3]	[0,15]	[0,25]	
FSD76-10				17/32 [13,5]	0.11 [2,8]	0.63 [16,0]	0.39 [10,0]	0.05 [1,3]	[0,15]	[0,25]	
FSD76-12				5/8 [15,9]	0.11 [2,8]	0.71 [18,0]	0.47 [12,0]	0.05 [1,3]	[0,15]	[0,25]	
FSD77-6	--	[1,00]	RED	3/8 [9,5]	0.12 [3,0]	0.49 [12,5]	0.24 [6,0]	0.06 [1,5]	[0,15]	[0,30]	
FSD77-8				15/32 [11,9]	0.12 [3,0]	0.57 [14,5]	0.31 [8,0]	0.06 [1,5]	[0,15]	[0,30]	
FSD77-10				17/32 [13,5]	0.12 [3,0]	0.65 [16,5]	0.39 [10,0]	0.06 [1,5]	[0,15]	[0,30]	
FSD77-12				5/8 [15,9]	0.12 [3,0]	0.73 [18,5]	0.47 [12,0]	0.06 [1,5]	[0,15]	[0,30]	
FSD78-6	16	[1,50]	BLACK	3/8 [9,5]	0.12 [3,0]	0.49 [12,5]	0.24 [6,0]	0.07 [1,8]	[0,15]	[0,30]	
FSD78-8				15/32 [11,9]	0.12 [3,0]	0.57 [14,5]	0.31 [8,0]	0.07 [1,8]	[0,15]	[0,30]	
FSD78-10				17/32 [13,5]	0.12 [3,0]	0.65 [16,5]	0.39 [10,0]	0.07 [1,8]	[0,15]	[0,30]	
FSD78-12				5/8 [15,9]	0.12 [3,0]	0.73 [18,5]	0.47 [12,0]	0.07 [1,8]	[0,15]	[0,30]	
FSD78-18				7/8 [22,2]	0.12 [3,0]	0.96 [24,5]	0.71 [18,0]	0.07 [1,8]	[0,15]	[0,30]	

NOTES:

- USED FOR:
 - STRANDED COPPER WIRE ONLY
 - 221°F [105°C] MAX. OPERATING TEMPERATURE
- MATERIAL:
 - STAMPING: COPPER, TIN PLATED
 - HOUSING: POLYPROPYLENE, COLOR CODED
- SEE www.panduit.com FOR PACKAGE QUANTITIES
- DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT
- FOR TOLERANCING REFER TO DIN 46228 PART 4

* DIES USED WITH CT-3001 OR CT-3001/E TOOL



PANDUIT PART #	WIRE RANGE		COLOR*	WIRE STRIP LENGTH +1/32 -0 [+0.8 -0]	MAX. WIRE INSUL. DIA.	DIMENSIONS in. [mm]					INSTALLATION TOOLS/DIES
	AWG	[mm ²]				L	P	ID-1	S1	S2	
FSD79-8	14	[2,08]	YELLOW	15/32 [11,9]	0.14 [3,6]	0.57 [14,5]	0.31 [8,0]	0.08 [2,1]	[0,15]	[0,30]	CT-1002 CT-1003 CT-1123
FSD80-8	14	[2,50]	BLUE	15/32 [11,9]	0.17 [4,2]	0.59 [15,0]	0.31 [8,0]	0.09 [2,3]	[0,15]	[0,30]	
FSD80-12				5/8 [15,9]	0.17 [4,2]	0.75 [19,0]	0.47 [12,0]	0.09 [2,3]	[0,15]	[0,30]	
FSD80-18	12	[4,00]	GRAY	7/8 [22,2]	0.17 [4,2]	0.98 [25,0]	0.71 [18,0]	0.09 [2,3]	[0,15]	[0,30]	
FSD81-10				17/32 [13,5]	0.19 [4,8]	0.69 [17,5]	0.39 [10,0]	0.11 [2,9]	[0,20]	[0,30]	
FSD81-12				5/8 [15,9]	0.19 [4,8]	0.79 [20,0]	0.47 [12,0]	0.11 [2,9]	[0,20]	[0,30]	
FSD81-18	10	[6,00]	YELLOW	7/8 [22,2]	0.19 [4,8]	1.02 [26,0]	0.71 [18,0]	0.11 [2,9]	[0,20]	[0,30]	
FSD82-12				5/8 [15,9]	0.24 [6,2]	0.79 [20,0]	0.47 [12,0]	0.14 [3,6]	[0,20]	[0,30]	
FSD82-18	8	[10,0]	RED	7/8 [22,2]	0.24 [6,2]	1.02 [26,0]	0.71 [18,0]	0.14 [3,6]	[0,20]	[0,30]	
FSD83-12				5/8 [15,9]	0.30 [7,5]	0.83 [21,0]	0.47 [12,0]	0.18 [4,6]	[0,20]	[0,30]	
FSD83-18				7/8 [22,2]	0.30 [7,5]	1.06 [27,0]	0.71 [18,0]	0.18 [4,6]	[0,20]	[0,30]	
FSD84-12	6	[16,0]	BLUE	5/8 [15,9]	0.35 [8,8]	0.91 [23,0]	0.47 [12,0]	0.24 [6,0]	[0,20]	[0,40]	
FSD84-18				7/8 [22,2]	0.35 [8,8]	1.14 [29,0]	0.71 [18,0]	0.24 [6,0]	[0,20]	[0,40]	
FSD85-16	4	[25,0]	YELLOW	3/4 [19,1]	0.43 [11,0]	1.14 [29,0]	0.63 [16,0]	0.30 [7,5]	[0,20]	[0,50]	
FSD85-18				7/8 [22,2]	0.43 [11,0]	1.22 [31,0]	0.71 [18,0]	0.30 [7,5]	[0,20]	[0,50]	
FSD85-22				1 [25,4]	0.43 [11,0]	1.38 [35,0]	0.87 [22,0]	0.30 [7,5]	[0,20]	[0,50]	
FSD86-16	2	[35,0]	RED	3/4 [19,1]	0.49 [12,5]	1.18 [30,0]	0.63 [16,0]	0.33 [8,5]	[0,20]	[0,50]	
FSD86-18				7/8 [22,2]	0.49 [12,5]	1.26 [32,0]	0.71 [18,0]	0.33 [8,5]	[0,20]	[0,50]	
FSD86-25	1-1/0	[50,0]	BLUE	1 1/8 [28,6]	0.49 [12,5]	1.26 [32,0]	0.98 [25,0]	0.33 [8,5]	[0,20]	[0,50]	
FSD87-20				15/16 [23,8]	0.59 [15,0]	1.42 [36,0]	0.79 [20,0]	0.41 [10,5]	[0,30]	[0,60]	
FSD87-25				1 1/8 [28,6]	0.59 [15,0]	1.61 [41,0]	0.98 [25,0]	0.41 [10,5]	[0,30]	[0,60]	
FSD89-20	2/0	[70,0]	YELLOW	15/16 [23,8]	0.63 [16,0]	1.46 [37,0]	0.79 [20,0]	0.50 [12,7]	[0,40]	[0,60]	
FSD89-27				1 1/4 [31,0]	0.63 [16,0]	1.73 [44,0]	1.06 [27,0]	0.50 [12,7]	[0,40]	[0,60]	
FSD90-25	3/0	[95,0]	RED	1 1/8 [28,6]	0.71 [18,0]	1.73 [44,0]	0.98 [25,0]	0.58 [14,7]	[0,40]	[0,60]	
FSD91-27	4/0-250	[120,0]	BLUE	1 1/4 [31,0]	0.83 [21,1]	1.89 [48,0]	1.06 [27,0]	0.66 [16,7]	[0,50]	[0,70]	
FSD92-32	300 kcmil	[150,0]	YELLOW	1 1/2 [37,0]	0.91 [23,1]	2.28 [58,0]	1.26 [32,0]	0.78 [19,7]	[0,50]	[25,40]	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
11	05.29.13	BDK	TMR	VMB	ADDED TOOL INFORMATION RELATED TO CT-3001 AND CT-3001E	A41667
10	01.19.13	BDK	BCT	VMB	REVISED AND REDRAWN; ADDED CSA LOGO	A41667

TITLE FERRULE - SINGLE WIRE WITH SLEEVE (DIN)		CUSTOMER DRAWING	
ITEM REVISION NAME N41667BA/11		DRAWING NUMBER A41667	
DATASET FILE NAME N41667BA_DC/11A		MATERIAL SEE NOTES	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN 1 mm			
DRAWN BY JKD		DATE 2/9/99	
CHK SKB		SCALE N.T.S.	
SHT 1 OF 1		SIZE B	