


LDPH10 OPEN POSITION



LDPH10 CLOSED POSITION

PANDUIT PART NO.	LENGTH	WEIGHT
LDPH10**6-A	72.00 ±.18 [1828.8 ±4.6]	.13 LBS/FT [.57 g/mm]
LDPH10**8-A	96.00 ±.18 [2438.4 ±4.6]	
LDPH10**10-A	120.00 ±.18 [3048.0 ±4.6]	
LDPH10**2-A	78.74 ±.18 [2000.0 ±4.6]	

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLORS AND/OR PACKAGE QUANTITY.
2. PART IS DESIGNED TO SUPPORT MAXIMUM WEIGHT ON A CLEAN, DRY, SMOOTH SURFACE. THE SURFACE MUST BE PROPERLY PREPARED IN ACCORDANCE WITH PANDUIT RECOMMENDATIONS.
3. TO APPLY PART (ADHESIVE BACKING INSTALLATION ONLY):
 - a. REMOVE PROTECTIVE FILM
 - b. PLACE PART IN DESIRE LOCATION
 - c. APPLY PRESSURE TO FLAT SURFACE ON RACEWAY
4. DIMENSIONS IN PARENTHESES ARE IN METRIC.
5. NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. THE CONDITIONS UNDER WHICH THESE RACEWAYS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.

CAD FILENAME/LAYERS  D38737BQ_DC_LDPH10_01B.PRT

PANDUIT CORP. TINLEY PARK, ILLINOIS

△ F HINGED LDPH10 RACEWAY
(LDPH10)
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± (.XXX) ±.010(.25)
(.XX) ±.03(.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
JBN

	MAT'L;
--	--------

DATE	09-22-04
------	----------

PVC

CHK'D	BKR
-------	-----

SCALE	NONE
-------	------

DRAWING NO.

38737-16

DWG
A
SIZE

-	-----	---	---	RELEASED TO PRODUCTION	-----	----	----			
-	-----	---	---	F. REVISED PART DESCRIPTION IN TITLE BLOCK E. REVISED NOTES: #2 AND #3	-----	----	----			
2	04-15-05	JBN	BKR	D. REVISED NOTATION C. REVISED DIMENSION: .058 WAS .055	38737-16	RGRO	RGRO			
1	02-24-05	JBN	BKR	B. REVISED CAD FILE NAME A. REVISED BASE AND COVER GEOMETRY						
R	09-22-04	JBN	BKR	DRAWING RELEASED						
REV	DATE	BY	CHK	DESCRIPTION	ECN	CHK	CUST	SUP		