

Specifications:

Oscillation Frequency (Hz)	1250 ± 200
Operating Voltage (Vp-p)	2.0 ~ 5.0
Rated Voltage (Vp-p)	3.0
Input Watt Max (W)	0.2
Sound Pressure Level Min. (dB)	85 at 10cm at Rated Voltage
Coil Resistance ()	8.0 ± 2
Operating Temperature (°C)	-20 ~ +70
Storage Temperature (°C)	-40 ~ +80
Housing	ABS 707 UL94HB plastic resin (Color: Black)
Leading Pin	Tin Plated Brass
Weight (Grams)	4.0
Options	For other options contact factory

PS: Vp-p = 1/2duty, square wave

Dimensions: (units: mm)