




CONTACT CONFIGURATION  
TIMING (BBM) NON-SHORTING




## NOTE:

1. ALL DIMENSIONS IN MM[INCH].
2. GENERAL TOLERANCE: X.X=± 0.4  
X.XX=± 0.25
3. TERM. NOS. FOR REFERENCE ONLY.
- ▲ 4. CONTACT MATERIAL: SILVER
5. CONTACT RATING: 150MILLIAMP, 250VAC/DC  
350MILLIAMP, 110VAC/DC
6. CONTACT RATING (NON-SWITCHING) 5A
7. OPERATING FORCE 425± 100CM/STANDARD
8. OPERATING TEMP: -30°C TO 85°C
- ▲ 9. CIRCUIT SP: 9 POSITION 30° INDEX.
10. DIELECTRIC STRENGTH: 1000V RMS MIN.@ SEA LEVEL.
- ▲ 11. HARDWARE SUPPLIED ON SWITCH:  
LOCKWASHER, HEXNUT, STOP RING
12. ▲ DENOTES CRITICAL PARAMETER.



ISOMETERIC



**E-SWITCH®**

TITLE KC19A30.001NLS

|     |        |                         |         |    |
|-----|--------|-------------------------|---------|----|
| A   | 14681  | RELEASED FOR PRODUCTION | 2/16/05 | AR |
| REV | PCR NO | DESCRIPTION             | DATE    | BY |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

|       |       |      |         |    |    |     |         |     |   |
|-------|-------|------|---------|----|----|-----|---------|-----|---|
| SCALE | 1.5:1 | DATE | 2/16/05 | DR | AR | DWG | G510588 | REV | A |
|-------|-------|------|---------|----|----|-----|---------|-----|---|