

4

3

2

1


LOC	DIST	REVISIONS					
P	LTR	DESCRIPTION			DATE	DWN	APVD
		REVISED PER ECO-11-005027			11MAR11	RK	HMR

NOTES:

MATERIALS:
HOUSING: POLYAMIDE, UL94V-0.
TERMINALS: COPPER ALLOY, TIN PLATED.
SCREWS: STEEL, ZINC PLATED.

ELECTRICAL:
RATING: 20A, 150V(300V LIMITED RATING)
UL & CSA.

MECHANICAL:
WIRE RANGE: 14-22 AWG.
MAXIMUM TIGHTENING TORQUE: 7 IN-LBS.



.500±.010	9.811	30	4WWV-30-008	4-796598-8	
	9.486	29	4WWV-29-008	4-796598-7	
	9.161	28	4WWV-28-008	4-796598-6	
	8.836	27	4WWV-27-008	4-796598-5	
	8.511	26	4WWV-26-008	4-796598-4	
	8.186	25	4WWV-25-008	4-796598-3	
	7.861	24	4WWV-24-008	796598-6	
	7.536	23	4WWV-23-008	4-796598-2	
	7.211	22	4WWV-22-008	4-796598-1	
	6.886	21	4WWV-21-008	4-796598-0	
	6.561	20	4WWV-20-008	3-796598-9	
	6.236	19	4WWV-19-008	3-796598-8	
	5.911	18	4WWV-18-008	3-796598-7	
	5.586	17	4WWV-17-008	3-796598-6	
	5.261	16	4WWV-16-008	7-1437649-5	
	4.936	15	4WWV-15-008	3-796598-5	
	4.611	14	4WWV-14-008	1-1546158-9	
	4.286	13	4WWV-13-008	3-796598-4	
	3.961	12	4WWV-12-008	3-796598-3	
	3.636	11	4WWV-11-008	3-796598-2	
.394±.010	3.311	10	4WWV-10-305	6-1437649-9	
	3.311	10	4WWV-10-008	1546119-4	
	2.986	9	4WWV-09-008	3-796598-1	
	2.661	8	4WWV-08-304	6-1437649-6	
	2.661	8	4WWV-08-008	1-1546158-8	
	2.336	7	4WWV-07-008	3-796598-0	
	2.011	6	4WWV-06-008	1-1546158-6	
	1.686	5	4WWV-05-008	5-1437649-9	
	.394±.010	1.361	4	4WWV-04-008	4-796598-9
	.500±.010	1.361	4	4WWV-04-008	5-1437649-5
	.500±.010	1.036	3	4WWV-03-008	1-1546158-5
	.500±.010	.711	2	4WWV-02-008	2-796598-9
	DIM "B"	DIM. "A"	NO. OF POS.	CATALOG NUMBER	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 5/19/04	STE TE Connectivity		
		CHK S YODER 5/19/04			
DIMENSIONS: INCHES		APVD S YODER 5/19/04	NAME		
		PRODUCT SPEC	4WWV-XX-008 ASSEMBLY		
		APPLICATION SPEC			
MATERIAL		WEIGHT	SIZE A3	CAGE CODE 00779	RESTRICTED TO
			C-5-1437649-5		
		CUSTOMER DRAWING	SCALE NTS	SHEET 1 OF 1	REV P