


15 mm carbon pre-set potentiometer series H/V A 15

- Closed version
- Both side setting, insulated slider
- Linear or logarithmic resistance law
- Resistance tolerance:
 $\pm 20\%$ for value $R \leq 1\text{M}\Omega$
 $\pm 30\%$ for value $R > 1\text{M}\Omega$
- On special request closer tolerances are available
- Mechanical endurance 10000 cycles




Rated dissipation at $\vartheta_{\text{amb}} = 40^\circ\text{C}$	lin 0.25W / log 0.12W
Resistance value range	lin 100Ω to $5\text{M}\Omega$ / log $2.2\text{K}\Omega$ to $2.5\text{M}\Omega$
Maximum voltage	lin 300V dc / log 200V dc
Electric angle of rotation	$250^\circ \pm 20^\circ$
Mechanical angle of rotation	$265^\circ \pm 5^\circ$
Operating torque	4 to 25 mNm
End stop torque	$\geq 100\text{ mNm}$
Weight	1.3 g approx.


HA 15 / 30 (10x12,5)




HA 15 / 30 (10x15)




VA 15 / 30 (5x5)



ADJUSTMENT SLOT



THUMBWHEEL



Thumbwheel Colour	Code
White	88 131 147
Black	88 131 388
Red	88 131 391
Blue	88 131 390
Green	88 131 392
Yellow	88 131 389