



Wiha SoftFinish® Handle - Standard Series



302 Slotted Screwdriver, With Wiha-SoftFinish® Handle

Round blade, high alloy CVM, hardened, hard chromed.
Wiha-Chromtop tips. Handle, multi-component, cushion grip.

Item No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
302 05*	3.0	.118	100	3.9	0.5	.020	204	8.0	.06	10
302 10*	3.5	.139	100	3.9	0.6	.024	204	8.0	.07	10
302 15*	4.0	.157	100	3.9	0.8	.031	211	8.3	.11	10
302 17*	4.0	.157	150	5.9	0.8	.031	261	10.3	.12	10
302 18*	4.5	.187	80	3.1	0.8	.031	191	7.5	.11	10
302 11*	4.5	.187	125	5.0	0.8	.031	236	9.3	.12	10
302 19*	4.5	.187	150	5.9	0.8	.031	261	10.2	.12	10
302 20*	5.5	.216	125	5.0	1.0	.039	236	9.3	.15	10
302 38*	5.5	.216	300	11.8	1.0	.039	411	16.1	.24	10
302 22*	6.0	.250	100	3.9	1.2	.047	218	8.6	.17	10
302 23	6.5	.255	100	3.9	1.0	.039	218	8.6	.20	10
302 25	6.5	.255	150	5.9	1.2	.047	268	10.6	.22	10
302 27	8.0	.315	150	5.9	1.2	.047	274	10.8	.29	10
302 30	8.0	.315	175	7.0	1.2	.047	299	11.8	.30	10
302 35	10.0	.393	200	8.0	1.6	.063	324	12.8	.36	10
302 36	12.0	.472	250	9.8	2.0	.078	374	14.7	.52	10

*Cabinet Tips



302 Stubby Slotted Screwdriver, With Wiha-SoftFinish® Handle

Item No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
302 39	4.0	.157	25	1.0	0.8	.031	75	2.95	.09	10
302 55	5.5	.216	25	1.0	1.0	.039	75	2.95	.09	10
302 65	6.5	.255	25	1.0	1.2	.047	75	2.95	.10	10



358 Square Screwdriver, With Wiha-SoftFinish® Handle

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
358 01	1	100	3.9	4.5	5/32	210	8.2	.12	10
358 02	2	150	5.9	5.0	1/4	268	10.5	.19	10
358 03	3	150	5.9	6.0	1/4	268	10.5	.22	10



311 Phillips Screwdriver, With Wiha-SoftFinish® Handle

Round blade, high alloy CVM steel, hardened, hard chromed.
Wiha-Chromtop tips. Handle, multi-component, cushion grip.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
311 05	0	60	2.4	3.0	.118	164	6.5	.06	10
311 10	1	80	3.1	4.5	.177	191	7.5	.11	10
311 12	1	200	8.0	4.5	.177	311	12.3	.15	10
311 14	1	300	12.0	4.5	.177	411	16.2	.18	10
311 15	2	100	3.9	6.0	.236	218	8.6	.20	10
311 17	2	200	8.0	6.0	.236	318	12.5	.25	10
311 18	2	300	12.0	6.0	.236	418	16.5	.30	10
311 20	3	150	5.9	8.0	.315	274	10.8	.33	10
311 25	4	200	8.0	10.0	.393	323	12.7	.51	10



311 Stubby Phillips Screwdriver, With Wiha-SoftFinish® Handle

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
311 35	1	25	1.0	4.5	.177	75	3.0	.09	10
311 40	2	25	1.0	6.0	.236	75	3.0	.10	10



313 Pozidriv® Screwdriver, With Wiha-SoftFinish® Handle

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
313 05	0	60	2.4	3.0	.118	164	6.5	.06	10
313 10	1	80	3.1	4.5	.177	191	7.5	.11	10
313 12	1	200	8.0	4.5	.177	311	12.3	.15	10
313 15	2	100	3.9	6.0	.236	218	8.6	.20	10
313 20	3	150	5.9	8.0	.315	274	10.8	.33	10