

datasheet for SEB 2600 G M4
article number: 972354105



product description:	order number: 972 354-105
description:	Safety built-in socket, 4 mm diameter, touch-protected, M 4 threaded connection and soldering hole, gold-plated brass. For installation into switchpanels and equipment chassis with wall thicknesses up to 6 mm. Accessory BES 1000. Installation hole: 12.2 mm diameter. Tightening torque: 50 Ncm.
typ:	SEB 2600 G M4 braun/braun
system:	4 mm safety system
order number:	972 354-105
color	
other color versions:	
technical data	
measurement category	CAT III
norm	DIN EN 61010-031
type of contact:	unsprung socket
type of termination:	screw / solder
rated voltage:	AC/DC 1000 V
rated current:	32 A
contact resistance:	5 mOhm
mounting:	screw
material	
contact material:	brass
contact surface material:	gold
housing material:	PA
connecting nut material:	brass nickel-plated
environmental conditions:	
temperature range:	-40°C to +80°C
flammable class:	
housing:	94 V-2
drawing	

