

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [130137-0178](#)  
**Status:** **Active**  
**Overview:** [Watertite® Wet-Location Wiring Solutions](#)  
**Description:** Super-Safeway® Multiple Outlet Box, Extended Depth, 2-Sided, Feed-Thru F3 (3/4"), (1) NEMA 5-15 GFCI Receptacles with Flip Lid, Open Neutral Relay, Top-of-Box GCM, 0.91m 12/3 SOOW Cord on Both sides, 5-15 Plug & Conn.



Series

image - Reference only

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

**Agency Certification**

CSA LR6837

**General**

|                             |                                                          |
|-----------------------------|----------------------------------------------------------|
| Product Family              | Power Distribution                                       |
| Series                      | <a href="#">130137</a>                                   |
| Enclosure Rating            | NEMA 4                                                   |
| GFCI Reset                  | Manual                                                   |
| Mounting Style              | Portable                                                 |
| Open Neutral Relay          | Yes                                                      |
| Overview                    | <a href="#">Watertite® Wet-Location Wiring Solutions</a> |
| Product Literature Order No | 987650-7737                                              |
| Product Name                | Super-Safeway™                                           |
| Receptacle Type             | GFCI Duplex                                              |
| Type                        | Multiple Outlet Box                                      |
| UPC                         | 78678875165                                              |
| Woodhead                    | Yes                                                      |

**Physical**

|                       |                 |
|-----------------------|-----------------|
| Cord Diameter         | 15.24mm (.600") |
| Cord Grip Body Size   | F3 3/4"         |
| Cord Length           | 1.83m (6.0')    |
| Feed-Thru             | Yes             |
| Flip Lid              | No              |
| Material - Housing    | Rubber          |
| Number of Receptacles | 1               |
| Packaging Type        | Carton          |

**Electrical**

|                               |           |
|-------------------------------|-----------|
| Cord Type                     | 12/3 SOOW |
| Current - Maximum per Contact | 15A       |
| GFCI                          | Yes       |
| Ground Continuity Monitor     | Yes       |
| NEMA Configuration            | NEMA 5-15 |
| Voltage - Maximum             | 125V      |

**Material Info**

|                 |           |
|-----------------|-----------|
| Old Part Number | 3080F-GFI |
|-----------------|-----------|

**EU RoHS**

**ELV and RoHS**

**Compliant**

**REACH SVHC**

**Not Reviewed**

**Low-Halogen Status**

**Not Reviewed**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[130137Series](#)