


Crocodile clips

MA 260 SH



Product	MA 260 SH
description	Contact-protected Miniature alligator clip with high strength insulation and nickel-plated bronze jaws. Clamping range up to a bolt diameter of 6 mm. The part of the jaws (fine wire section) allows a secure contact to be made when clamping even the thinner wire. 4 mm diameter brass socket connection.
operating instruction	BA465
article-no. / *colour	● 00 black ● 01 red Ni
drawing	
	
technical data	
connection	unsprung socket 4 mm
rated voltage ⁽¹⁾	AC/DC 300 V
measurement cat. acc. to IEC 61010	CAT II
rated current ⁽¹⁾ (consider derating curve)	15 A
material socket	bronze, nickel plated
housing material	PA
temperature range acc. To IEC61010 ⁽²⁾	-25 °C to +80 °C
flammability class acc. to UL 94 (only valid for basic material of housing)	HB
clamping range	6 mm
standard	IEC 61010

4 mm safety system

⁽¹⁾ for normal environmental conditions -5°C to +40°C

⁽²⁾ contact the manufacturer for applications at deviating temperature ranges
stand: 19.06.2019