




FEATURES:

- Fits cable types 174, 179, 187
- Supplied with center conductor and sleeve

MATERIALS:

Body and Fitting – Brass per QQ-S-764, Type 303, Cond. A

Center Contact – Gold Plated Brass per QQ-B-626, Alloy 360, ½ Hard

Dielectric – PTFE

Gaskets and Seals: Silicone Rubber

Finish:

Body and Fitting: Passivated steel

Center Contact: Hard gold, per MIL-G-45204, Type II, Class 2

RATINGS:

Nominal Impedance: 50 Ohms

ORDERING INFORMATION: Model 4804

All dimensions are in inches. Tolerances (except noted): $.xx = \pm .02"$ (.51 mm), $.xxx = \pm .005"$ (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA




FIGURE #1

- A. Slide shrink tubing and crimp sleeve over cable.
- B. Strip cable as shown.
- C. Flair braid outward slightly by rotating Dielectric.

FIGURE #2

- D. Place center contact over center conductor, provide gap as shown and solder.

FIGURE #3

- E. Place connector body over contact sliding barrel under braid.
- F. Push sleeve up against the body of the connector and crimp.

FIGURE #4

- G. Push shrink tubing over crimped sleeve so it touches the connector body and shrink the sleeve using a heat gun or equivalent.

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies.

Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

4804